

CAT. N° 0 048 54



## IP2X TERMINAL BLOCK - PHASE (BLACK) - 1 X 6 TO 25<sup>2</sup> - 12 X 1.5 TO 16<sup>2</sup> -L. 113 MM

Pack (number of units)	10
Volume (dm <sup>3</sup> )	1,315
Weight (g)	697,00

### Product characteristics

#### Distribution terminal blocks

- Conform to standard IEC 60998-2-1
- Supplied ready for use (screws not tightened)
- 100 A max. - 400 V~ with 25 mm<sup>2</sup> input
- 80 A max. - 400 V~ with 16 mm<sup>2</sup> input

#### IP 2X terminal blocks

- Mounting on rail with universal support Cat.No 0 048 11, or on 12 x 2 flat bar
- Phase
- black
- Number of connections : 1 x 6 to 25 + 12 x 1.5 to 16 mm<sup>2</sup>
- Length : 113 mm

### General characteristics

#### Distribution terminal blocks

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.198\)](#)
- [Description page \(p.200\)](#)

#### Agreements & certificates of conformity

- [OC / CB - FR\\_633370/M2](#)

#### Installation & technical data

- [F00193EN-02](#)