

CAT. N° 0 225 56



ISOLATING SWITCH VISTOP - 160 A - 4P - SIDE HANDLE, BLACK - 9 MODULES

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 2,312 |
| Weight (g) | 857,00 |

Product characteristics

63 to 160 A

- Possibility to add auxiliary contact Cat.No 0 227 07

160 A

- Side handle
- 4P
- Connection : Key 6 sides
- No of 17.5 mm modules : 9

General characteristics

Vistop™ isolating switches - 32 to 160 A

- Safety switches for on-load circuit breaking by visible isolation of the contacts
- Double break type load switching with self cleaning contacts by rapid make and break movements
- Fixing on rail EN 60715 or screw fixing (only on rail for Vistop 63 A)
- Padlockable handle in open position: 1 to 3 padlocks Cat.No 0 227 97
- 2 versions for mounting on faceplate:
 - right side handle, supplied with seal to maintain the IP protection for the enclosures (up to IP 55), screws, self adhesive drilling template, extension rod (30 to 170 mm) for creating an external angle
 - direct front handle or external (for Vistop 63 to 160 A)

Documentation

Catalogue pages & additional information

- [Description page \(p.166\)](#)
- [Vistop™ isolating switches](#)

Installation & technical data

- [F00185EN/04](#)

Installation instructions & related documents

- [0064DG2/06](#)

Agreements & certificates of conformity

- [OC / CB - FR2991/41630020](#)