

CAT. N° 0 676 86



LED LAMP FOR ILLUMINATED TWO-WAY SWITCH CELIANE/MOSAIC 230 V

Pack (number of units)	10
Volume (dm ³)	0,188
Weight (g)	22,00

Product characteristics

Accessories

Locator lights

- For illuminated function of Cat.Nos 0 770 02/12, 0 792 02/12, 0 770 32/42 and 0 792 32/42
- Connected by direct mounting
- White
- 230 V. Consumption 0.15 mA

General characteristics

Mosaic™ Programme mechanisms - pushbuttons and accessories

Documentation

Catalogue pages & additional information

- [Description page \(p.506\)](#)
- [Selection chart \(p.508\)](#)
- [Selection chart \(p.512\)](#)
- [Description page \(p.877\)](#)

Agreements & certificates of conformity

- NF - NF012_1596
- OC / CB - FR_703331
- NF - 677822/A1
- OC / CB - 677823/A1
- VDE - 40044639
- OC / CB - FR_703340
- NF - NF012_1595

Installation & technical data

- [F01956EN/01](#)

Environmental product profile

- [Environnemental product sheet n°A E2404A-FR](#)
- [Environnemental product sheet n°A E2407A-FR](#)