

CAT. N° 6 462 00



LINKEO FIX 19" CABINET WITH FIX SIDE PANELS - CAPACITY 6U - DIMENSIONS 358X600X450 MM - READY- ASSEMBLED

Pack (number of units)	1
Volume (dm ³)	101,651
Weight (g)	20 000,00

Product characteristics

Linkeo fix 19" cabinets

Fix side panels

- Delivered ready-assembled
- Depth 450 mm
- Capacity : 6 U
- Height : 358 mm
- Width : 600 mm
- Loading capacity : 18 kg

General characteristics

Linkeo 19" and 10" wall-mounting cabinets

- IP 20 - IK 08
- Equipped with:
 - 1 reversible door made of screen-printed safety glass and with integrated lock
 - 2 x 19" uprights with U marking and adjustable in depth
 - 3 pre-cut cable entries (top, bottom and rear). 1 brush for a cable entry. Top perforations for natural ventilation
 - panels with automatic grounding (ready assembled version)
 - earthing kit (flatpack version)
- Anthracite grey RAL 7016

Documentation

Catalogue pages & additional information

- [Description page \(p.784\)](#)
- [Technical page \(p.790\)](#)
- [Technical page \(p.791\)](#)

Installation & technical data

- [F02824EN-00](#)
- [FT0437_CABLO_GS](#)

Installation instructions & related documents

- [LE10110AA-01](#)

CAT. N° 6 462 00

Spare parts

CAT. NO.	DESCRIPTION	UNIT PRICE	MINIMUM ORDER QUANTITY
981080	SET OF 2 HINGES FOR LINKEO WALLMOUNTING CABINET	5.84	1
981082	LOCKING KIT (BARREL AND KEY) FOR LINKEO DOOR	12.75	1
981083	SET OF 2 KEYS (CODE 9473) FOR LINKEO RAL7016 DOOR AND SIDE PANELS	5.84	1
981084	LINKEO RAL7016 COMPLETE DOOR 6UX19" (MOUNTED, FLATPACK AND PIVOTING VERSION)	63.14	1

Spare Parts Guarantee

Does not affect the guarantee for the finished product.

Spare parts guaranteed against defects if exchanged within 2 weeks.