

CAT. N° 6 045 65

LOCKING SYSTEM FOR XL<sup>3</sup>-N 630 DISTRIBUTION BOARDS

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

## Product characteristics

## Accessories

- Locking system for XL<sup>3</sup>-N 630 distribution boards

## General characteristics

XL<sup>3</sup>-N 630 3-phase distribution boards - from 12 to 54 poles (outgoing terminals)

- 3-phase distribution boards for moulded case circuit breakers, DRX or DPX<sup>3</sup>; IP 40 (IP 42 with the kit Cat.No 6 045 68) - IK 08 with door
- Conform to standard IEC 61439-2.Type tested; tested and certified by third part laboratory; Maximum voltage 415 V~
- Rated peak withstand current (Ipk): up to 110 kA
- Ambient temperature: 50 °C continuously; Grey RAL 7035;
- Supplied with: surface mounting box, door with handle, faceplate, fully isolated tin plated copper busbar
- The number of holes of earth and neutral terminal blocks are equal to the number of outgoing devices

## Documentation



## Catalogue pages &amp; additional information

- [Description page \(p.213\)](#)