

CAT. N° 4 098 10

**MCB - DX³ - 25 KA - 1P - 230/400 V~ - 32 A - D CURVE**

Pack (number of units)	1
Volume (dm ³)	0,332
Weight (g)	239,00

Product characteristics**Single pole 230/400 V~**

- D curve
- Nominal rating I_n : 32 A
- Number of modules : 1.5

General characteristics**MCBs DX³ - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves**

- Breaking capacity:
 - 25 kA - IEC 60947-2 - 400 V~
 - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation**Catalogue pages & additional information**

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

**Environmental product profile**

- [Environnemental product sheet n°8 E0084A-FR](#)

**Agreements & certificates of conformity**

- [LOVAG - IT 13.030](#)