

CAT. N° 4 101 62


MCB - DX³ - 50 KA - 3P 400 V~ - 20 A - C CURVE

Pack (number of units)	1
Volume (dm ³)	1,04
Weight (g)	668,00

Product characteristics
3-pole - 400 V~

- C curve
- Nominal rating I_n : 20 A
- Number of modules : 4.5

General characteristics
MCBs DX³ - 50 kA - thermal magnetic MCBs from 10 A to 63 A - C and D curves

- Breaking capacity:
 - 50 kA - IEC 60947-2 - 400 V~
 - Can be equipped with DX³ auxiliaries and accessories

Documentation

Catalogue pages & additional information

- [Description page \(p.069\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


Installation & technical data

- [F01220EN/01](#)


Environmental product profile

- [Environnemental product sheet n°8 E0084A-FR](#)


Installation instructions & related documents

- [LE03603AB](#)


Agreements & certificates of conformity

- [LOVAG - IT 14.021](#)