

CAT. N° 4 102 17


**MCB - DX<sup>3</sup> - 50 KA - 3P 400 V~ - 40 A - D CURVE**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,04
Weight (g)	677,00

**Product characteristics**
**3-pole - 400 V~**

- D curve
- Nominal rating I<sub>n</sub> : 40 A
- Number of modules : 4.5

**General characteristics**
**MCBs DX<sup>3</sup> - 50 kA - thermal magnetic MCBs from 10 A to 63 A - C and D curves**

- Breaking capacity:
- 50 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX<sup>3</sup> auxiliaries and accessories

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.069\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Installation & technical data**

- [F01220EN/01](#)

 **Installation instructions & related documents**

- [LE03603AB](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0084A-FR](#)