

CAT. N° 4 093 62


**MCB - DX<sup>3</sup> 10000 - 16 kA - 4P 400 V~ - 80 A - C CURVE**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,04
Weight (g)	926,00

**Product characteristics**
**4-pole 400 V~**

- C curve
- Nominal rating I<sub>n</sub> : 80 A
- Number of modules : 6

**General characteristics**
**MCBs DX<sup>3</sup> 10000 - 16 kA - thermal magnetic circuit breakers from 1 A to 125 A - B and C curves**

- Conform to IEC 60898-1
- Compatible with prong-type and fork type supply busbars (except 80 A, 100 A and 125 A MCBs)
- Breaking capacity
  - 10000 - IEC 60898-1 - 400 V~
  - 16 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries, motorised controls and add-on modules

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.066\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Installation & technical data**

- [F01204EN-01](#)

 **Installation instructions & related documents**

- [LE03603AB](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0084A-FR](#)