

CAT. N° 4 196 67

**MCB RX³ 4500 - 1P - 230/400 V~ - 32 A - C CURVE**


| | |
|---------------------------|----------|
| Pack (number of units) | 12 |
| Volume (dm ³) | 2,012 |
| Weight (g) | 1 688,00 |

Product characteristics**Single pole 230/400 V~**

- C curve
- Nominal rating I_n : 32 A
- Number of modules : 1

General characteristics**MCBs RX³ 4500 - thermal magnetic MCBs from 6 A to 63 A - C curve**

- Conform to IEC 60898-1
- Do not accept auxiliaries, and add-on modules
- Compatible with prong-type supply busbars
- Breaking capacity:
 - 4500 - IEC 60898-1 - 230/400 V~
 - 4.5 kA - IEC 60947-2 - 230/400 V~
 - 6000 - IEC 60898-1 - 127/220 V~
 - 6 kA - IEC 60947-2 - 127/220 V~

Documentation **Catalogue pages & additional information**

- [Description page \(p.051\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [OC / CB - IT 16504](#)
- [VDE - 40042042](#)
- [VDE - 40044433](#)
- [SNI - PCS 00498.01](#)

 **Installation & technical data**

- [F01911EN-01](#)

 **Environmental product profile**

- [Environnemental product sheet n°20 E0162B-EN](#)