

CAT. N° 4 197 01


MCB RX³ 4500 - 2P - 230/400 V~ - 40 A - C CURVE

Pack (number of units)	6
Volume (dm ³)	1,864
Weight (g)	1 679,00

Product characteristics
2-pole 230/400 V~

- C curve
- Nominal rating I_n : 40 A
- Number of modules : 2

General characteristics
MCBs RX³ 4500 - thermal magnetic MCBs from 6 A to 63 A - C curve

- Conform to IEC 60898-1
- Do not accept auxiliaries, and add-on modules
- Compatible with prong-type supply busbars
- Breaking capacity:
 - 4500 - IEC 60898-1 - 230/400 V~
 - 4.5 kA - IEC 60947-2 - 230/400 V~
 - 6000 - IEC 60898-1 - 127/220 V~
 - 6 kA - IEC 60947-2 - 127/220 V~

Documentation

Catalogue pages & additional information

- [Description page \(p.051\)](#)
- [Dimensions of din-rail equipment](#)


Agreements & certificates of conformity

- [OC / CB - IT 16504](#)
- [VDE - 40042042](#)
- [VDE - 40044433](#)
- [SNI - PCS 00498.01](#)


Installation & technical data

- [F01911EN-01](#)


Environmental product profile

- [Environnemental product sheet n°20 E0162B-EN](#)