

REF . 4 192 29

**MCB RX³ 6000 - 2P - 230/400 V~ - 50 A - C CURVE - PRONG/FORK TYPE SUPPLY BUSBARS**


| | |
|-------------------------------------|----------|
| Emballage (nombre number of units) | 6 |
| Volume (dm ³) | 1,864 |
| Poids (g) | 1 771,00 |

Caractéristiques du produit**2-pole 230/400 V~**

- C curve
- Nominal rating In : 50 A
- Number of modules : 2

Caractéristiques générales**MCBs RX³ 6000 - thermal magnetic MCBs from 6 A to 63 A - C curve**

- Conform to IEC 60898-1
- Do not accept auxiliaries, and add-on modules
- Compatible with prong-type supply busbars
- Breaking capacity:
 - 6000 - IEC 60898-1 - 230/400 V~
 - 6 kA - IEC 60947-2 - 230/400 V~
 - 10000 - IEC 60898-1 - 127/220 V~
 - 10 kA - IEC 60947-2 - 127/220 V~

Documentation associée **Catalogue pages & additional information**

- [Description page \(p.052\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [OC / CB - IT-14270](#)
- [VDE - 40041249](#)
- [IMQ - IT-14270](#)

 **Installation & technical data**

- [F01909EN-02](#)

 **Environmental product profile**

- [Environnemental product sheet n°20 E0161B-EN](#)