

CAT. N° 4 034 36

**MCB TX<sup>3</sup> 6000 - 1P - 230/400 V~ - 25 A - C CURVE - PRONG/FORK TYPE SUPPLY BUSBARS**

Pack (number of units)	10
Volume (dm <sup>3</sup> )	1,619
Weight (g)	1 379,00

**Product characteristics****Single pole 230/400 V~**

- C curve
- Nominal rating In : 25 A
- Number of modules : 1

**General characteristics****MCBs TX<sup>3</sup> 6000 - thermal magnetic MCBs from 2 A to 63 A - B & C curve**

- Conform to IEC 60898-1
- Compatible with prong-type and fork type supply busbars
- Equipped with special DIN rail clamp allowing independent MCB removal with supply busbar in place
- Breaking capacity:
  - 6000 - IEC 60898-1 - 230/400 V~
  - 6 kA - IEC 60947-2 - 230/400 V~
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls
- Do not accept add-on modules

**Documentation****Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

**Agreements & certificates of conformity**

- VDE - 40042432
- OC / CB - IT-15813
- OC / CB - IT - 15108