

CAT. N° 4 036 07

**MCB TX³ 6000 - 2P - 230/400 V~ - 20 A - C CURVE - PRONG-TYPE SUPPLY BUSBARS**

Pack (number of units)	5
Volume (dm ³)	1,635
Weight (g)	1 031,00

Product characteristics**2-pole 230/400 V~**

- C curve
- Nominal rating In : 20 A
- Number of modules : 2

General characteristics**MCBs TX³ 6000 - thermal magnetic MCBs from 6 A to 63 A - C curve**

- Conform to IEC 60898-1
- Compatible with prong-type supply busbars
- Breaking capacity:
 - 6000 - IEC 60898-1 - 230/400 V~
 - 6 kA - IEC 60947-2 - 230/400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- Do not accept add-on modules

Documentation **Catalogue pages & additional information**

- [Description page \(p.053\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [VDE - 40039791](#)
- [AENOR - 030/002306](#)

 **Installation & technical data**

- [F1569EN/01](#)