

CAT. N° 0 270 05

**MCCB - DRX 125 - THERMAL MAGNETIC - ICU 10 KA - 415 V~ - 3P - IN 50 A**

Pack (number of units)	1
Volume (dm ³)	1,215
Weight (g)	732,00

Product characteristics**DRX 125****Breaking capacity Icu 10 kA (415 V~)**

- 3P
- 50 A

General characteristics**DRX™ 125 - thermal magnetic MCCBs from 15 to 125 A**

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
 - M5 terminal for $I_n \leq 50$ A and M8 range for $I_n > 50$ A
 - Fixing screws
 - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2, in compliance with NEMA

Documentation**Catalogue pages & additional information**

- [Description page \(p.127\)](#)
- [Technical page \(p.128\)](#)
- [DRXTM 125](#)

**Agreements & certificates of conformity**

- [OC / CB - SE 57100](#)