

CAT. N° 0 270 42



MCCB - DRX 125 - THERMAL MAGNETIC - ICU 25 KA - 220/240 V~ - 1P - 25 A

| | |
|---------------------------|--------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 0,632 |
| Weight (g) | 345,00 |

Product characteristics

DRX 125

Breaking capacity Icu 25 kA (220/240 V~)

- 1P
- Icu 25 kA (240 V~)
- 25 A

General characteristics

DRX™ 125 - thermal magnetic MCCBs from 15 to 125 A

- For switching, control, isolation and protection of low-voltage electrical lines
- Can be fitted with auxiliaries
- Supplied with:
 - M5 terminal for In ≤ 50 A and M8 range for In > 50 A
 - Fixing screws
 - Insulating shields (2 for 3P and 3 for 4P)
- Fixed thermal and magnetic
- Conform to IEC 60947-2, in compliance with NEMA

Documentation



Catalogue pages & additional information

- [Description page \(p.127\)](#)
- [Technical page \(p.128\)](#)
- [DRXTM 125](#)