

CAT. N° 4 223 90



## MCCB DPX<sup>3</sup> 1600 - S2 ELEC RELEASE + CENTRAL - 4P - ICU 100 KA (400 V~) - IN 800 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	48
Weight (g)	19 535,00

### Product characteristics

#### MCCBs electronic release S2 with energy metering central unit fixed version

- Adjustment of  $I_r$ ,  $I_{sd}$ ,  $t_r$ ,  $t_{sd}$
- Instantaneous protection  $I_f = 20$  kA
- Green indicator lamp
- Connector for test unit
- Logic and dynamic selectivity

#### Breaking capacity $I_{cu}$ 100 kA (400 V~)

- 4P
- $I_n$  : 800 A

### General characteristics

#### DPX<sup>3</sup> 1600 - S2 electronic release MCCBs from 630 to 1600 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with residual current relays
- Supplied complete with:
  - connection plates for bars
  - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.151\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)
- [DPX<sup>3</sup> 1600](#)

#### Installation & technical data

- [F01964EN01](#)
- [ModbusTable\\_18](#)

#### Installation instructions & related documents

- [LE07037AA](#)
- [LE07038AB](#)
- [LE08865AB](#)
- [LE08866AB](#)

#### Firmwares

- [Legrand Power Control Station software](#)