

REF . 4 223 24



MCCB DPX³ 1600 - S2 ELECTRONIC RELEASE - 3P - Icu 70 KA (400 V~) - IN 800 A



Emballage (nombre number of units)	1
Volume (dm ³)	48
Poids (g)	15 395,00

Caractéristiques du produit

MCCBs electronic release S2 fixed version

- Adjustment of Ir, Isd, tr, tsd
- Instantaneous protection If = 20 kA
- Green indicator lamp
- Connector for test unit
- Logic and dynamic selectivity

Breaking capacity Icu 70 kA (400 V~)

- 3P
- In : 800 A

Caractéristiques générales

DPX³ 1600 - S2 electronic release MCCBs from 630 to 1600 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with residual current relays
- Supplied complete with:
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation associée

Catalogue pages & additional information

- [Description page \(p.151\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 1600](#)

Installation & technical data

- [F01964EN/01](#)
- [MODBUS TABLE 14](#)

Installation instructions & related documents

- [LE07037AA](#)
- [LE07038AB](#)
- [LE08866AB](#)
- [LE08865AB](#)

Firmwares

- [Legrand Power Control Station software](#)