

CAT. N° 4 222 85

**MCCB DPX³ 1600 - THERMAL MAGNETIC - 3P+N/2 - ICU 70 KA (400 V~) - IN 1250 A**

Pack (number of units)	1
Volume (dm ³)	48
Weight (g)	18 733,00

Product characteristics**MCCBs thermal magnetic release fixed version**

- Thermal adjustable from 0.8 to 1 In
- Magnetic adjustable from 5 to 10 In

Breaking capacity Icu 70 kA (400 V~)

- 3P + N/2
- In : 1250 A

General characteristics**DPX³ 1600 - thermal magnetic release MCCBs from 630 to 1250 A**

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with residual current relays
- Supplied complete with:
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation**Catalogue pages & additional information**

- [Description page \(p.150\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 1600](#)

**Installation instructions & related documents**

- [LE07037AA](#)