

CAT. N° 4 222 64



MCCB DPX³ 1600 - THERMAL MAGNETIC RELEASE - 3P - Icu 50 KA (400 V~) - IN 800 A

Pack (number of units)	1
Volume (dm ³)	48
Weight (g)	13 851,00

Product characteristics

MCCBs thermal magnetic release fixed version

- Thermal adjustable from 0.8 to 1 In
- Magnetic adjustable from 5 to 10 In

Breaking capacity Icu 50 kA (400 V~)

- 3P
- In : 800 A

General characteristics

DPX³ 1600 - thermal magnetic release MCCBs from 630 to 1250 A

- Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines
- Can be fitted with auxiliaries
- Can be used with residual current relays
- Supplied complete with:
 - connection plates for bars
 - insulated shields (phase barriers)
- Conform to IEC 60947-2 - Sealable adjustment
- Can be mounted on plate in XL³ cabinets and enclosures

Documentation

Catalogue pages & additional information

- [Description page \(p.150\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 1600](#)

Installation & technical data

- [F01963EN01DPX3_1600MT_ENGv5](#)

Installation instructions & related documents

- [LE07037AA](#)