

REF . 4 201 24


**MCCB THERMAL MAGNETIC - DPX³ 160 - ICU 50 KA 400 V~
- 3P - 80 A**


Emballage (nombre number of units)	1
Volume (dm ³)	1,814
Poids (g)	1 173,00

Caractéristiques du produit
MCCBs - fixed version

- Thermal adjustable from 0,8 to 1 In
- Magnetic fixed at 10 In (fixed at 400 A for In 16 A and 25 A)

Breaking capacity Icu 50 kA (400 V~)

- 3P
- In : 80 A

Caractéristiques générales
DPX³ 160 thermal magnetic - MCCBs from 16 to 160 A

- Can be mounted on rail or on plate in XL³ cabinets and enclosures
- MCCBs for switching, control isolation and protection of low voltage electrical lines
- Supplied with fixing screws cage terminals 70 mm² max. (flexible cable) or 95 mm² max. rigid cable with accessories
- Can be fitted with DPX³ 160 and 250 common auxiliaries and accessories
- Conform to IEC 60947-2

Documentation associée
 **Catalogue pages & additional information**

- [Technical page \(p.074-075\)](#)
- [Description page \(p.136\)](#)
- [Technical page \(p.137\)](#)
- [Technical page \(p.143\)](#)
- [Technical page \(p.134-135\)](#)
- [DPX³ 160 & 250](#)
- [DPX³ 160/250/630 & 1600](#)

 **Installation & technical data**

- [F01360EN/03](#)

 **Installation instructions & related documents**

- [Y4220E](#)

 **Agreements & certificates of conformity**

- [OC / CB - 71483](#)
- [OC / CB - 71479](#)