

REF . 0 527 82

**MOBILE SOCKET HYPRA - IP44 - 200/250 V~ - 32 A - 2P+E - PLASTIC**


Emballage (nombre number of units)	1
Volume (dm ³)	1,676
Poids (g)	330,00

Caractéristiques du produit**LV mobile sockets****200 to 250 V~ 50/60 Hz - 32 A 2P+E**

- Plastic
- 32 A

Caractéristiques générales**Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A**

- Conform to IEC 60309-1 and IEC 60309-2
- IP 44 according to IEC 60529
- IK 09: plastic and rubber
- IK 10: metal according to IEC 62262
- Self-extinguishing:
 - 850°C (support of active parts) / 960 °C for Prinsinter)
 - 650 °C: plastic housing conform to IEC 60695-2-10
 - 50°C to + 100°C (- 20°C for Prinsinter)

Documentation associée **Catalogue pages & additional information**

- [Selection chart \(p.390-391\)](#)
- [Technical page \(p.392\)](#)
- [Hypra](#)

 **Agreements & certificates of conformity**

- [OC / CB - FR_701476](#)

 **Installation & technical data**

- [F00138EN/03](#)