

CAT. N° 0 538 94


**MOBILE SOCKET HYPRA - IP44 - 380/415 V~ - 63 A - 3P+N+E - RUBBER**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	4,935
Weight (g)	1 434,00

**Product characteristics**
**LV mobile sockets**
**380 to 415 V~ 50/60 Hz - 63 A 3P+N+E**

- Rubber
- 63 A

**General characteristics**
**Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A**

- Conform to IEC 60309-1 and IEC 60309-2
- IP 44 according to IEC 60529
- IK 09: plastic and rubber
- IK 10: metal according to IEC 62262
- Self-extinguishing:
  - 850°C (support of active parts) / 960 °C for Prinsinter)
  - 650 °C: plastic housing conform to IEC 60695-2-10
  - 50°C to + 100°C (- 20°C for Prinsinter)

**Documentation**
 **Catalogue pages & additional information**

- [Technical page \(p.392\)](#)

 **Installation & technical data**

- F00138EN-03

 **Installation instructions & related documents**

- [LE09817AA](#)

 **Agreements & certificates of conformity**

- [OC / CB - FR\\_700640](#)