

CAT. N° 5 556 09


MOBILE SOCKET P17 PRO - IP66/67 - 380/415 V~ - 125 A - 3P+N+E

Pack (number of units)	1
Volume (dm ³)	7,88
Weight (g)	1 680,00

Product characteristics
Mobile sockets
380/415 V~

- 125 A
- 3P+N+E

General characteristics
P 17 Tempra Pro IP 66/67 LV 63 and 125 A
Documentation

Catalogue pages & additional information

- [Selection chart \(p.381\)](#)


Agreements & certificates of conformity

- [OC / CB - FR_706516](#)
- [CCC - CQC2018010203055870](#)


Installation & technical data

- [F02385EN-01](#)


Environmental product profile

- [Environnemental product sheet n°9 E0060B-EN](#)