

CAT. N° 4 173 60



## MPCB MPX<sup>3</sup> 63H - THERMAL MAGNETIC - MOTOR PROTECTION - 3P - 10 A - 100 KA

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,408
Weight (g)	1 002,00

### Product characteristics

#### Thermal magnetic MPCBs

- Adjustable thermal release
- Magnetic release 13 Ie max.

#### MPX<sup>3</sup> 63H

- High breaking capacity
- With rotary handle
- Fixing on rail or by screw
- 3-phase motor 400/415 V : 4 kW
- Thermal release adjustment range : 6 to 10 A
- Magnetic release operating current : 130 A
- 415 V breaking capacity Icu : 100 kA

### General characteristics

#### MPCBs MPX<sup>3</sup> - motor protection circuit breakers from 0.16 A to 100 A

- Conform to IEC 60947-1, IEC 60947-2, IEC 60947-4 ; class 10

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.184\)](#)
- [Technical page \(p.182-183\)](#)
- [MPCBs MPX3](#)



#### Installation & technical data

- [F01988EN-05](#)



#### Installation instructions & related documents

- [LE07207AB](#)



#### Environmental product profile

- [Environnemental product sheet n°8 E0083A-EN](#)