

CAT. N° 0 240 37



## OSMOZ ILLUM STANDARD HANDLE SELECTOR SWITCH - 2 STAY-PUT POSITIONS (0-12H) - BLACK

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,08
Weight (g)	20,00

### Product characteristics

#### Selector switches

##### With standard handle

- Black
- Positions : 2 stay-put positions - 45°

### General characteristics

#### Osmoz control and signalling units: illuminated heads

- Supplied with a fixing ring
- IP 66, IP 69K
- Conform to IEC 60947-5-1

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.352\)](#)
- [Technical page \(p.355\)](#)
- [Osmoz: control and signalling units](#)

#### Environmental product profile

- [Environnemental product sheet n°8 E0070A-EN](#)

#### Agreements & certificates of conformity

- [OC / CB - FR 60044591B/1](#)
- [VERITAS \(BV\) - 16400/CO BV](#)
- [UL recogn cUL - NKCR8.E57818](#)