

CAT. N° 0 239 54



OSMOZ NON ILLUMINATED KEY SELECTOR SWITCH - 2 STAY-PUT POSITIONS 90°

Pack (number of units)	1
Volume (dm ³)	0,08
Weight (g)	45,00

Product characteristics

Selector switches

With key

- Black button
- 2 stay-put positions - 90°
- Key free in both positions

General characteristics

Osmoz control and signalling units: non-illuminated heads

- Supplied with a fixing ring
- IP 69, IP 69K
- Conform to IEC 60947-5-1

Documentation



Catalogue pages & additional information

- [Description page \(p.351\)](#)
- [Technical page \(p.355\)](#)
- [Osmoz: control and signalling units](#)



Agreements & certificates of conformity

- [OC / CB - FR 60044591B/1](#)
- [VERITAS \(BV\) - 16400/CO BV](#)
- [UL recogn cUL - NKCR8.E57818](#)