

CAT. N° 7 530 65



## PASSTHROUGH TV-R-SAT SOCKET VALENA IN'MATIC

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,536
Weight (g)	133,00

### Product characteristics

#### Passthrough sockets

- Installation in case of maintenance
- Amplifier and a line balancing are recommended
- TV male connector (Ø9.5 mm): 5-68/120-862 MHz
- R female connector (Ø9.5 mm): 87.5-108 MHz
- SAT "F" type connector: 950-2400 MHz
- Recommended coaxial cable: 17/19 VATC
- Visual check of the connection
- Attenuation: 14 dB

#### TV-R-SAT socket

- TV: 5-68/120-862 MHz
- R: 87.5-108 MHz
- SAT: 950-2400 MHz

### General characteristics

#### Valena™ IN'MATIC mechanisms - TV sockets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.499\)](#)
- [Selection chart \(p.509\)](#)
- [Selection chart \(p.513\)](#)
- [Valena, Synergy and MosaicTMProgramme - TV sockets](#)

#### Installation & technical data

- [F02112EN-00](#)

#### Installation instructions & related documents

- [LE07425CC](#)