

CAT. N° 0 363 00


PLINTH FOR ATLANTIC E CABINET - 600X300 - RAL 7021

Pack (number of units)	1
Volume (dm ³)	35
Weight (g)	6 696,00

Product characteristics
Plinths RAL 7021

- Height 200 mm
- Front and rear trap door
- For cabinets Width : 600 mm
- For cabinets Depth : 300 mm
- Weight : 6 kg

General characteristics
Atlantic metal cabinets supplied with plain plate - IP 55/IP 66 - IK 10 - Type 4x - Type 12

- IP 66 according to standards IEC EN 60529 for 1-door cabinets - IP 55 according to standards IEC EN 60529 for 2-door cabinets
- IK 10 according to standards IEC EN 62262
- LCIE 17 07 90 10A
- Type 4x, 1 door, Type 12, 2 doors - cULus, Bureau Veritas
- EMC attenuation 20 dB (for an EMC attenuation from 40 to 50 dB at 1 GHz, please consult us)
- Excellent resistance to corrosion and chemical agents
- 80 µm thick textured polyester coating. Anti-corrosion treatment for hinges and pins
- Reversible door - Fitted with lever
- Supplied with double bar lock - Self-centering positioning system for the equipment
- Compatible with all Atlantic accessories Low cable entries RAL 7035 - Optional depth adjustment for cabinets 400 mm depth, with slide rails Cat.No 0 367 45

Documentation

Catalogue pages & additional information

- [Selection chart \(p.288-289\)](#)
- [Description page \(p.290\)](#)
- [Technical page \(p.295\)](#)
- [Technical page \(p.296\)](#)


Installation instructions & related documents

- [041401-01](#)