

CAT. N° 4 125 15



## POWER CONTACTOR CX<sup>3</sup> - WITH 24 V~ COLL AND HANDLE - 2P 250 V~ - 40 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,369
Weight (g)	255,00

### Product characteristics

#### Power contactors with 24 V~ coil and handle

- Manual override for test and repair function, carried out via the handle
- Permanent "ON" or "OFF" without automatic reset

#### 2-pole - 250 V~

- Handle can be accessed after removing blanking plate
- I max : 40 A
- Type of contact : 2 N/O
- Number of modules : 2

### General characteristics

#### Power contactors with handle CX<sup>3</sup> - from 16 A to 63 A

- Conform to IEC/EN 61095
- Space for power supply busbar on top (up to 25 A)

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.086\)](#)
- [Technical page \(p.088\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- [CCC - 2014010304745275](#)
- [NF - 608293A](#)
- [VDE - 40034227](#)
- [QC / CB - 608293C](#)

#### Installation & technical data

- [F01333EN/01](#)

#### Environmental product profile

- [Environnemental product sheet n°8 E0073A-EN](#)