

REF . 1 350 32



PRACTIBOX S FLUSH-MOUNTING CABINET FOR DRY PARTITION WITHOUT TERMINAL BLOCKS - SMOKED DOOR - 2 ROWS - 12 MODULES PER ROW



Emballage (nombre number of units)	1
Volume (dm ³)	15,059
Poids (g)	1 446,00

Caractéristiques du produit

Cabinets supplied without terminal blocks

- Smoked Transparent door
- Number of rows : 2
- Number of modules per row : 12
- Total number of modules : 24
- Height : 385 mm
- Width : 328 mm
- Depth : 103 mm

Caractéristiques générales

Practibox S - flush-mounting cabinets for dry partitions from 4 to 72 modules

- Allows to achieve assemblies conform to IEC 61439-3
- IP40 IK07
- Class II
- Plastic material
- Supplied with door
- For dry partitions
- 850° fireproof flush-mounting plastic boxes

Documentation associée

Catalogue pages & additional information

- [Description page \(p.217\)](#)
- [Technical page \(p.219\)](#)

Installation & technical data

- [F02564EN-02](#)

Environmental product profile

- [Environnemental product sheet n°A E4067A-EN](#)

Installation instructions & related documents

- [LE10835AA_05](#)

Agreements & certificates of conformity

- [LOVAG - IT 18.173](#)
- [OC / CB - FR_703887/M1](#)