

REF . 1 340 18



PRACTIBOX S FLUSH-MOUNTING CABINET FOR MASONRY WITHOUT TERMINAL BLOCKS - SMOKED DOOR - 1 ROW WITH 8 MODULES PER ROW



Emballage (nombre number of units)	1
Volume (dm ³)	6,641
Poids (g)	600,00

Caractéristiques du produit

Cabinets supplied without terminal blocks

- Smoked Transparent door
- Number of rows : 1
- Number of modules per row : 8
- Total number of modules : 8
- Height : 225 mm
- Width : 256 mm
- Depth : 100 mm

Caractéristiques générales

Practibox S - flush-mounting cabinets for masonry from 4 to 72 modules

- Allows to achieve assemblies conform to IEC 61439-3
- IP40 IK07
- Class II
- Plastic material
- Supplied with door
- For brick and masonry walls
- 650° fireproof flush-mounting plastic boxes

Documentation associée

Catalogue pages & additional information

- [Description page \(p.216\)](#)
- [Technical page \(p.219\)](#)

Installation & technical data

- [F02564EN-02](#)

Environmental product profile

- [Environnemental product sheet n°A E4067A-EN](#)

Installation instructions & related documents

- [LE10835AA_05](#)

Agreements & certificates of conformity

- [LOVAG - IT 18.173](#)
- [OC / CB - FR_703887/M1](#)