

REF . 7 522 35



PROGRAMMABLE THERMOSTAT VALENA IN'MATIC - IVORY



Emballage (nombre number of units)	1
Volume (dm ³)	0,887
Poids (g)	256,00

Caractéristiques du produit

Thermostats

- Screw terminals

Programmable thermostats

- Supplied with cover plate
- Provides temperature regulation for oil, gas and electric heating installations in comfort, reduced and frost-free modes
- Weekly programming
- Permanent display of the current programme
- 4 preset programmes, 1 free programme, 4 time periods max. per day, 2 adjustable temperature levels. Manual switching possible
- Adjustment range: 7 °C to 30 °C. Adjustment accuracy: ± 0.5 °C
- Permanent backup of programmes. Working reserve 100 hrs
- 1 output per changeover contact
- Power supply: 230 V~ 50/60Hz. Switching capacity: 8 A - 250 V~ resistive circuit
- To be completed with a 5-module plate (Valena Life or Valena Allure). Supplied with Cat.No 0 801 02 Batibox multimaterial 2-gang box (depth 40 mm)
- Ivory Valena Life / Valena Allure (common Cat.No)

Caractéristiques générales

Valena™ IN'MATIC mechanisms - thermostats and ventilation controls

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation associée



Catalogue pages & additional information

- [Description page \(p.498\)](#)



Installation instructions & related documents

- [LE07429AB](#)
- [LE08584AA](#)