

CAT. N° 4 126 30



## PROGRAMMABLE TIME SWITCH DIGITAL DISP. - MULTIFUNCTION ANNUAL PROG. - 2 OUTPUTS

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,638
Weight (g)	199,00

### Product characteristics

#### 2 outputs multiple functions annual programme - 5 years clock working reserve

- Programme settings: on daily, weekly or yearly basis 15 languages
- A programme consists of a on and off time and their assignment to certain days
- Option to suspend the programme for a specific period to set-up with start and date
- Minimum programme setting: 1 s.
- High precision clock:  $\pm 0.1$  sec per day
- Programmed directly on keypad, or using program transfer key Cat.No 4 128 72

#### Power supply 230 V~ - 50/60 Hz

- 2 outputs - 230 V~ - 50/60 Hz
- Astronomical function
- $2 \times 3 \times 28 = 168$  programmes
- Number of modules : 2

### General characteristics

#### Programmable time switches - with digital display

- For switching an electric circuit (lighting, heating) ON or OFF at selected times during a pre-programmed time period
- Temporary (automatic return) or permanent (forced switching ON or OFF) override on output

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.090\)](#)
- [Technical page \(p.091\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- [VDE - 40035703](#)

#### Installation instructions & related documents

- [292573GB02](#)