

CAT. N° 7 522 62



PUSH-DIMMER VALENA LIFE - 240 V~ - 50 HZ - WITH COVER PLATE - IVORY

Pack (number of units)	1
Volume (dm ³)	0,824
Weight (g)	144,00

Product characteristics

Dimmers 240 V~ - 50 Hz

- Equipped with overvoltage and short-circuit protection
- When switched on, lights up at the level set before last switch-off
- Can be remotely controlled via non-illuminated push-buttons (Cat.No 7 520 11), with each push-button able to perform the ON/OFF and dimming function

Push-dimmer without neutral

- For all types of lamps:
 - dimmable LEDs: 5 W to 75 W (10 lamps max.)
 - dimmable compact fluorescent lamps: 5 W to 75 W (10 lamps max.)
 - halogen with ferromagnetic or electronic transformer: 3 VA to 400 VA
 - fluorescent tube - ballast: 3 VA to 200 VA
 - halogen and incandescent 240 V: 3 W to 400 W
- When switched on, gradually (2 seconds) lights up at the level set before last switch-off
- Functioning:
 - dimming mode
 - pre-set level mode (0%, 33%, 66% and 100%)
 - nightlight mode: dimming of the lamp for 1 hour
- Ivory

General characteristics

Valena™ Life - dimmers with cover plate

- Valena In'Matic mechanisms supplied with cover plates and support frames
- To be equipped with plates
- Supplied with mounted dust protection transparent shield
- Flowpack packaging: robust protection to ensure optimum operation

Documentation

Catalogue pages & additional information

- [Description page \(p.518\)](#)

Installation & technical data

- [F01602EN-04](#)

Installation instructions & related documents

- [LE07457AB](#)