

CAT. N° 4 111 31



## RCBO - DX<sup>3</sup> 6000 - 6 KA - 1P+N 230 V~ - 16 A - 30 MA - A TYPE - N LEFT HAND

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,257
Weight (g)	150,00

### Product characteristics

#### Single pole + neutral - 230 V~

- Neutral on left-hand side

#### A Type 30 mA

- C curve
- Nominal rating I<sub>n</sub> : 16 A
- Number of modules : 1

### General characteristics

#### RCBOs DX<sup>3</sup> 6000 - 6 kA - residual current circuit breakers from 6 A to 32 A - A type

- Conform to IEC 61009-1
- Compatible with prong-type supply busbars
- Voltage dependent tripping
- Breaking capacity:
  - 6000 - IEC 61009-1 - 6 kA / IEC 60947-2 for single pole + neutral
- A type : detect AC and DC component faults
- Enhanced immunity to unwanted tripping in disturbed environments
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.060\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

#### Installation & technical data

- [F02071EN/01](#)

#### Environmental product profile

- [Environnemental product sheet n°A E0065A-EN](#)

#### Installation instructions & related documents

- [LE09580AA](#)

#### Agreements & certificates of conformity

- [CCC - 2017010307963924](#)
- [OC / CB - 689349/A1](#)