

CAT. N° 4 115 64

**RCCB TX³ - 2P 230 V~ - 100 MA - 25 A - A TYPE**

Pack (number of units)	1
Volume (dm ³)	0,39
Weight (g)	205,00

Product characteristics**2-pole - 230 V~****A type**

- Sensitivity : 100 mA
- In : 25 A
- Number of modules : 2

General characteristics**RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

Documentation **Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- VDE - 40041196
- OC / CB - CB FR_700536
- OC / CB - CB FR_704741

 **Installation & technical data**

- [F01575EN/02](#)