

CAT. N° 4 030 00



RCCB TX³ - 2P 230 V~ - 30 MA - 25 A - AC TYPE - DO NOT ACCEPT AUXILIARIES

Pack (number of units)	1
Volume (dm ³)	0,38
Weight (g)	206,00

Product characteristics

2-pole - 230 V~

AC type

- Sensitivity : 30 mA
- In : 25 A
- Number of modules : 2

General characteristics

RCCBs TX³ - residual current circuit breakers - from 25 A to 63 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Do not accept auxiliaries

Documentation

Catalogue pages & additional information

- [Description page \(p.053\)](#)
- [Dimensions of din-rail equipment](#)

Agreements & certificates of conformity

- [OC / CB - CB FR_700536](#)
- [OC / CB - CB FR_704741](#)
- [VDE - 40036431](#)
- [VDE - 40036431](#)

Installation & technical data

- [F01540EN/02](#)