

CAT. N° 4 115 76


**RCCB TX<sup>3</sup> - 2P 230 V~ - 300 MA - 63 A - A TYPE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,39
Weight (g)	202,00

**Product characteristics**
**2-pole - 230 V~**
**A type**

- Sensitivity : 300 mA
- In : 63 A
- Number of modules : 2

**General characteristics**
**RCCBs TX<sup>3</sup> residual current circuit breakers - from 16 A to 80 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)


**Agreements & certificates of conformity**

- VDE - 40041196
- OC / CB - CB FR\_700536
- OC / CB - CB FR\_704741


**Installation & technical data**

- [F01575EN/02](#)