

CAT. N° 4 117 19


RCCB TX³ - 4P 400 V~ - 100 mA - 63 A - AC TYPE

Pack (number of units)	1
Volume (dm ³)	0,701
Weight (g)	337,00

Product characteristics
4-pole 400 V~

- Neutral on right-hand side

AC type

- Sensitivity : 100 mA
- In : 63 A
- Number of modules : 2

General characteristics
RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

Documentation

Catalogue pages & additional information

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)


Agreements & certificates of conformity

- [VDE - 40041193](#)
- [QC / CB - C FR_705078](#)
- [QC / CB - CB-FR_700757](#)
- [VDE - 40041193](#)


Installation & technical data

- [F01576EN/02](#)