

CAT. N° 4 117 64

**RCCB TX³ - 4P 400 V~ - 30 MA - 25 A - A TYPE**

Pack (number of units)	1
Volume (dm ³)	0,701
Weight (g)	333,00

Product characteristics**4-pole 400 V~**

- Neutral on right-hand side

A type

- Sensitivity : 30 mA
- In : 25 A
- Number of modules : 2

General characteristics**RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

Documentation**Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

**Agreements & certificates of conformity**

- [QC / CB - C.FR_705078](#)
- [QC / CB - CB-FR_700757](#)
- [VDE - 40041196](#)
- [VDE - 40041196](#)

**Installation & technical data**

- [F01576EN/02](#)