

CAT. N° 4 117 34



RCD DX³-ID - 4P 400 V~ NEUTRAL RIGHT HAND SIDE - 63 A - 500 MA - AC TYPE

Pack (number of units)	1
Volume (dm ³)	0,701
Weight (g)	348,00

Product characteristics

4-pole - 400 V~ - neutral on right-hand side

AC type

- Sensitivity : 500 mA
- In : 63 A
- Number of modules : 4

General characteristics

RCCBs - DX³-ID - residual current circuit breakers 16 A to 100 A - AC, A, F and B types

- Conform to IEC 61008 - 1, IEC 62423 (B type and F type)
- Compatible with prong-type and fork type supply busbars
- AC type : detect sinusoidal AC residual currents
- A type : detect sinusoidal AC and pulsating DC residual currents
- F type (High immunity) : detect AC and pulsating DC residual currents
- Enhanced immunity to unwanted tripping in disturbed environments
- Detection of high frequency fault currents
- B type : detect sinusoidal AC, pulsating DC and smooth DC residual currents
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation

Catalogue pages & additional information

- [Description page \(p.057\)](#)
- [Technical page \(p.058\)](#)
- [Dimensions of din-rail equipment](#)

Installation & technical data

- [F01590EN/02](#)

Installation instructions & related documents

- [LE03774](#)

Agreements & certificates of conformity

- [OC / CB - CB-FR_700719](#)
- [VDE - 40032163](#)
- [OC / CB - C FR_705078](#)
- [VDE - 40032163](#)
- [NF - NF012_1106](#)