

CAT. N° 4 020 63


**RCD LR - 4P 400 V~ - 40 A - 30 MA - AC TYPE**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,701
Weight (g)	337,00

**Product characteristics**
**4-pole - 400 V~ neutral on right-hand side**
**AC type**

- Sensitivity : 30 mA
- In : 40 A
- Number of modules : 4

**General characteristics**
**RCCBs RX<sup>3</sup> - residual current circuit breakers from 25 A to 63 A - AC and A types**

- Conform to IEC 61008-1
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Compatible with prong-type and fork type supply busbars
- Do not accept auxiliaries

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.050\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [OC / CB - CB FR\\_705078](#)
- [OC / CB - CB-FR\\_700757](#)
- [VDE - 40034493](#)
- [VDE - 40034493](#)

 **Installation & technical data**

- [F01536EN-02](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0013C-EN](#)