

CAT. N° 7 338 81



## RCD SOCKET OUTLET SYNERGY - ELR - DOUBLE POLE 30 MA - 1 GANG - 13 A 250 V~ - METALCLAD

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	178,00

### Product characteristics

#### RCD sockets 13 A - 250 V~

- Conform to BS 7288: 1990 and BS 1363 - Part 2: 1995
- Conventional earth pin release shutter
- Maximum operating current 16 A
- Electronic RCD module with a membrane switch for "test and reset"
- Flush mounting back box : min. 25 mm deep

#### ELR - DP 30 mA

- Trips in the event of a power failure
- Ideal for applications where it is desirable to automatically re-activate equipment after a power failure
- E.g. fridge, freezer, unmanned areas
- 1 gang
- Nominal plate dimensions: 86 x 86 mm

### General characteristics

#### Synergy™ - British standard socket outlets, RCD sockets and fused connection units - Metalclad

- Front plates: grey epoxy coated steel
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Supplied complete with close fit 43 mm deep surface-mounting back box

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.599\)](#)

#### Installation & technical data

- [F02521EN/00](#)

#### Installation instructions & related documents

- [LE08955AA](#)