

CAT. N° 0 205 84



REVERSIBLE FLAT GLASS DOOR XL³ 4000 - WIDTH 725 MM

Pack (number of units)	1
Volume (dm ³)	55,772
Weight (g)	19 954,00

Product characteristics

Reversible doors

- Supplied with handle
- Interchangeable key barrels, to be ordered separately
- For mounting on front, rear or side

Flat - glass

- Width 725 mm
- Height : 2000 mm

General characteristics

Distribution enclosures XL³ 4000

- IP 30 - IK 07
- IP 55 - IK 08 with door and sealing kit for use when joining enclosures
- Consist of the combination of a "roof-base" assembly, structural uprights, functional uprights, rear and side panels RAL 7035, plinths RAL 7004
- Height 2000 or 2200 mm.
- Capacity 24 modules (enclosures width 725 or width 975 with internal cable sleeve), 36 modules (enclosures width 975)
- Usable faceplate height 1800 mm (1700 mm only if using the pivoting support frame) or 2000 mm

Documentation

Catalogue pages & additional information

- [Description page \(p.267\)](#)
- [Selection chart \(p.268\)](#)
- [XL3 4000 equipment for mounting on adjustable plates](#)

Agreements & certificates of conformity

- [LOVAG - IT 12.019](#)
- [LOVAG - IT 12.017](#)
- [LOVAG - IT 12.019](#)

Installation instructions & related documents

- [F0996C/02](#)