

CAT. N° 6 514 32



## RIGID CONDUIT - WITH COUPLING - SHOCK RESISTANCE 2 JOULES - Ø EXT. 32 MM

Pack (number of metres)	15
Volume (dm <sup>3</sup> )	23
Weight (g)	3 600,00

### Product characteristics

#### Medium impact rigid conduits with integrated coupling

- PVC without Pb, Sn, Cd (RoHS compliant)
- Non flame propagating
- Surface-mounting or flush-mounting
- Suitable for prefabricated concrete. Conforming to European standard: EN/IEC 61386-21
- Crush resistance: 750 Newtons. Impact resistance: 2 joules at - 5 °C
- Min operating t°: - 5 °C ; Max operating t°: + 60 °C
- IK 07
- Can be used outside
- Supplied wrapped in film. Light grey (RAL 7035)
- Length of tubes: 3 m
- Ø exterior : : 32 mm
- Ø interior : : 27.8 mm
- thickness : : 2.10 mm

### General characteristics

#### Rigid conduits

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.624\)](#)

#### Agreements & certificates of conformity

- [NF 004 - 60050610D1](#)

#### Installation & technical data

- [F01719EN-01](#)