

CAT. N° 7 530 40



RJ 45 CATEGORY 5E DATA SOCKET VALENA IN'MATIC - UTP

Pack (number of units)	10
Volume (dm ³)	3,802
Weight (g)	55,00

Product characteristics

Data sockets Cat. 5e

- With LCS2 connector with fast connection thanks to integrated crimping
- Take AWG 22 single-core cables up to AWG 26 and AWG multicore cables
- Contacts marked with dual colour code and wiring schemes 568 A and 568 B
- Conform to standards ISO/IEC 11801 Ed. 2.0, amendment 2, EN 50173-1 and TIA/EIA 568 C2

RJ 45 socket Cat. 5e

- UTP

General characteristics

Valena™ IN'MATIC mechanisms - data, fibre optic and telephone sockets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation



Catalogue pages & additional information

- [Description page \(p.500\)](#)
- [Selection chart \(p.510\)](#)
- [Selection chart \(p.514\)](#)



Installation & technical data

- [F02115EN-00](#)



Installation instructions & related documents

- [LE07421AB](#)