

CAT. N° 0 343 28



SCREWLESS CONNECTION TERMINAL NYLBLOC AUTO - FOR 8 WIRES - 24 A - 450 V~

Pack (number of units)	50
Volume (dm ³)	0,908
Weight (g)	299,00

Product characteristics

Screwless connection terminals - Nylbloc auto

- No tool direct connection after simple stripping of copper conductors
- Test socket for tester screwdriver or test tip Cat.No 0 394 45 for IP 2X test or Ø4 mm tip on Nylbloc auto terminals
- Conform to EN 60998-2-2
- For rigid cable from 0.75 to 2.5 mm²
- Stripping length: 11 mm
- Connection by separate crimping blades. Transparent base providing full visibility of the connections
- Colour code to identify products
- Duplix marking possible on 3, 5 and 8-wire terminals
- Max. intensity: 24 A
- Insulating voltage: 450 V~
- Grey terminal for 8 wires

General characteristics

Nylbloc™ auto - screwless connection terminals

Documentation



Catalogue pages & additional information

- [Description page \(p.630\)](#)



Agreements & certificates of conformity

- [IMQ - CA02.01935](#)
- [AENOR - 030/002395](#)
- [NF - 650685A](#)