

CAT. N° 6 170 68



SHAVER SOCKET BELANKO - 115/230 V - 2 GANG

Pack (number of units)	1
Volume (dm ³)	2,177
Weight (g)	708,00

Product characteristics

Shaver socket

- Conform to BS 61558
- 115/230 V - 20 VA - 50/60 Hz
- Surface or flush-mounting, back box to be min. 47 mm deep - 2 gang

General characteristics

Belanko™ - hotel equipment

- Colour: White T084
- Material: Thermoplastic with glossy finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

Documentation



Catalogue pages & additional information

- [Description page \(p.550\)](#)



Installation & technical data

- [F01055EN/01](#)