

CAT. N° 7 300 66



## SOCKET OUTLET SYNERGY - 1 GANG SWITCHED - 13 A 250 V~ - WHITE

Pack (number of units)	10
Volume (dm <sup>3</sup> )	2,955
Weight (g)	1 085,00

### Product characteristics

#### Socket outlets 13 A - 250 V~

- Conform to BS 1363: Part. 2
- For flush-mounting, back box to be min. 25 mm deep
- With safety shutter mechanism
- ASTA licence

#### Single pole - switched

- 1 gang
- Nominal plate dimensions: 86 x 86 mm

### General characteristics

#### Synergy™ - British standard socket outlets - white

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.581\)](#)

#### Agreements & certificates of conformity

- [QC / CB - SE-90885](#)
- [ASTA - 780](#)

#### Installation & technical data

- [F00167EN-00](#)